






SECTION A-A
SCALE 1:1



PCB.WELDING DRAWING (TOLERANCE:±0.05)

技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC, DC.


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

型号	CKT	A	B
A420E1L2-2W2P12	2*1	0.00	5.40
A420E1L2-2W4P12	2*2	4.20	9.60
A420E1L2-2W6P12	2*3	8.40	13.80
A420E1L2-2W8P12	2*4	12.60	18.00
A420E1L2-2W10P12	2*5	16.80	22.20
A420E1L2-2W12P12	2*6	21.00	26.40
A420E1L2-2W14P12	2*7	25.20	30.60
A420E1L2-2W16P12	2*8	29.40	34.80
A420E1L2-2W18P12	2*9	33.40	39.00
A420E1L2-2W20P12	2*10	37.80	43.20
A420E1L2-2W22P12	2*11	42.00	47.40
A420E1L2-2W24P12	2*12	46.20	51.60

2	端子Contact	黄铜	N*1	表面镀锡
1	基座Wafer	PA66 UL94V-2	1	白色
序号	名称	材料	数量	备注

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X	±0.20	X.*	±10°	PART NO.
.XX	±0.10	.X*	± 8°	A420E1L2-2WXP12
.XXX	±0.05	.XX*	± 5°	DESIGN: Ethan
UNITS	mm	CHED: Olvia	MANUFACTURE DWG	
MATERILA	— — —	APPD: Ava		SCALE
FINISH	— — —			SHEET
			N:A	1/2

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X	±0.20	X.*	±10°	PART NO.
.XX	±0.10	.X*	± 8°	A420E1L2-2BXP12
.XXX	±0.05	.XX*	± 5°	DESIGN: Ethan
UNITS	mm	CHED: Olvia	MANUFACTURE DWG	
MATERILA	— — —	APPD: Ava		SCALE
FINISH	— — —			SHEET
			N:A	2/2