





一、 MATERIAL:

- 1. Insulator:PBT+30%Glass Fiber
- 2. Contact:Brass
- 3. Contact Plated:Gold Flash over Tin Or Glod Plated Or Tin Plated
- 4. Shell:Steel,Nickel Plated

二、 SPECIFICATION:

- 1. Current Rating:3 AMPS
- 2. Insulation Resistance: 1000MΩ MIN. At 500VDC
- 3. Dielectric Strength: 500V for One minute
- 4. Operation Temperature: -55° C~+105° C.

＊【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	DSUB-DS1037-09MN	DR9M双锁
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1