





RoHS



MATERIAL:

INSULATOR: HIGH TEMPERATURE THERMOPLASTIC, UL 94V-0

CONTACT: COPPER ALLOY

SHELL: SUS

PLATING:

CONTACT: PLATED 50U" NI OVER ALL CONTACT AU 1U

SHELL: PLATED 50U" NI OVERALL

PLATED 1U" AU SELECTIVE CONTACT AREA

ELECTRICAL:

CURRENT RATING: 0.5MA

VOLTAGE RATING: 5V AC/DC

AMBIENT TEMPERATURE RANGE: -40 °C ~ +85 °C

STORAGE TEMPERATURE RANGE: -40 °C ~ +85 °C

AMBIENT HUMIDITY RANGE: 95% R. H. MAX.


CONTACT RESISTANCE: 100M MAX. Ω

INSULATION RESISTANCE: 1000M MIN. /500VDC Ω

REFLOW PEAK TEMP: 260 °C


MATING CYCLES: 5000MIN INSERTIONS

Salt spray time: 24H



MICRO SIM CARD

Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A



PAD AREA

KEEP OUT AREA

RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ±0.05

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X ±0.30 X.* ±5°

.XX ±0.20 X.X* ±1°

.XXX ±0.10 X.XX* ±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
MICRO SIM 6P 1.35H

DESIGN: James

CHED: Talen

APPD: Sophia

TITLE:
MICRO SIM CARD PUSH
PUSH 6PIN H1.35


CUSTOMER

SIZE
A4UNITS
MM

SCALE

SHEET

N:A 1/1



RoHS

客户拉出方向

客户拉出方向

自粘上贴

纸箱底部和顶部各垫一块珍珠棉

护角

纸箱


封箱胶带

外箱标签贴示位置

将10卷产品放入箱内

NOTES

- 1. 每卷包装数量: 1000PCS/ 每卷
- 2. 卷带包装方式:



- 3. 每箱包装数量: 10000PCS/ 箱
- 4. 纸箱 350mm*350mm*440mm (内部尺寸), 材质 K=K

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	MICRO SIM 6P 1.35H	MICRO SIM CARD PUSH PUSH 6PIN H1.35
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE
		APPD: Sophia	UNITS
			A4
			MM
			SCALE
			N:A
			SHEET
			1/1