



防护等级 (Ingress protection)	IP50
插拔测试 (Plugging and unplugging test)	<2000次
产品耐温 (The product is temperature resistant)	-45° C / +135° C
测试电压 (kV rms) 针芯-针芯	1.2
额定电流Current rating	8A
电线尺寸Wire size	22-30AWG
导体接触规格 Conductor contact specifications	Ø0.9

外壳材料 Housing material	PC
绝缘体材料 Insulator material	PPS（可选PEEK） PPS（optional PEEK）
触体材料 Contact material	锡青铜镀金Contact material

未注公差 tolerances are not noted	
0~5	±0.10
6~10	±0.15
10~50	±0.20
51~100	±0.25
100+	±0.25%

TONGRUI JOIN — 阿 迈 通 瑞 —			东莞市通瑞电子科技有限公司 Dongguan Tongrui Electronic Technology Co., Ltd				
设计 DESIGNED		名称 PARTNAME	1P塑料双固定焊接插座红前螺母4Pin	视图 view	 	比例 SCALE	1:1
校对 CHECKED		型号 Model	1P. PKG. MO. 4. CL. GR	单位 UNIT	mm	版本 REV	A/0
审核 APPROVED		图号 DRAWING NO.		官网 Official website		www.cntfre.com	