









技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC, DC
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$

Part No	CKT	A	B	C	D
NH1.0-2PLT-MR	2	1.00	2.52	4.00	3.00
NH1.0-3PLT-MR	3	2.00	3.52	5.00	4.00
NH1.0-4PLT-MR	4	3.00	4.52	6.00	5.00
NH1.0-5PLT-MR	5	4.00	5.52	7.00	6.00
NH1.0-6PLT-MR	6	5.00	6.52	8.00	7.00
NH1.0-7PLT-MR	7	6.00	7.52	9.00	8.00
NH1.0-8PLT-MR	8	7.00	8.52	10.00	9.00
NH1.0-9PLT-MR	9	8.00	9.52	11.00	10.00
NH1.0-10PLT-MR	10	9.00	10.52	12.00	11.00
NH1.0-11PLT-MR	11	10.00	11.52	13.00	12.00
NH1.0-12PLT-MR	12	11.00	12.52	14.00	13.00
NH1.0-13PLT-MR	13	12.00	13.52	15.00	14.00
NH1.0-14PLT-MR	14	13.00	14.52	16.00	15.00
NH1.0-15PLT-MR	15	14.00	15.52	17.00	16.00
NH1.0-16PLT-MR	16	15.00	16.52	18.00	17.00



适用线路板(PCB LAYOUT)

常规



适用线路板(PCB LAYOUT)

端子焊脚加固

序号	品名	材质
①	1.0-B型立式WTB胶芯	PA10T UL94V-0米白色
②	1.0-B型立式WTB端子	铜合金/表面镀锡
③	1.0-B型立式WTB焊片	铜合金/表面镀锡
④	1.0-B型立式WTB吸盖	LCP UL94V-0 本色
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd
UNLESS OTHERWISE SPECIFIED TOLERANCES		
DECIMALS:	ANGLES:	TITLE: 1.0 Pitch B型立式WTB
X.:±0.50	±1°	PAR NH1.0-NPLT-MR
X.X:±0.20		DWN Lucas
X.XX:±0.10		CHKD Ethan
		APVD Jacob
		SCALE:1:1 UNIT:MM
		SIZE:A4 SHEET:1F1 REV:A
CUSTOMER COPY		