




1

2


3

4

5

REV.	DESCRIPTION	ECN NO.	NAME	DATE

-, MATERIAL:
1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated
-, SPECIFICATION:
1. Current Rating: 3 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: $-55^{\circ}\text{C} \sim +105^{\circ}\text{C}$
* 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®		
DIM. x. x.x x.xx		TOL. ±0.30 ±0.25 ±0.15		TITLE: DR9M叉锁				
GENERAL ANGLE: x. x.x x.xx		±5.0° ±2.0° ±1.0°		DWG. NO.: D-USB-18-0816-9PWZ		CHECKED: MAX		
				PART NO.: D-USB-18-0816-9PWZ		DRAWN: ELLA		
						APPROVED: WILL		
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn		