





修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	WANG	2017-02-10



Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	1.00	2.30	12P	11.00	12.30
3P	2.00	3.30	13P	12.00	13.30
4P	3.00	4.30	14P	13.00	14.30
5P	4.00	5.30	15P	14.00	15.30
6P	5.00	6.30	16P	15.00	16.30
7P	6.00	7.30	17P	16.00	17.30
8P	7.00	8.30	18P	17.00	18.30
9P	8.00	9.30	19P	18.00	19.30
10P	9.00	10.30	20P	19.00	20.30
11P	10.00	11.30			

SPECIFICATIONS:

Current Rating: 1A AC,DC
Voltage Rating: 50V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 20MΩ Max.
Insulation Resistance: 100MΩ Min.
Withstanding Voltage: 500V AC/minute
Material: Nylon 66,UL94V-0(White)



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111216 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称 : 10035HS-HNNG	
X.X	±0.30	X.X°	±3°	APPD: 核准 :	XIE
X.XX	±0.30	X.XX°	±2°	CHECK: 校对 :	WANG
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图 :	WANG
				PART NO: 产品编号 :	10035HS-H06G-HDGC1002
		DATE	SCALE	UNIT	CODE NUMBER
		2017-02-10	8:1	mm	A008