





-、MATERIAL:
1.Insulator:PBT+30%Glass Fiber
2.Contact:Brass
3.Contact Plated:Gold Flash over Tin Or
Glod Plated Or Tin Plated
4.Shell:Steel,Nickel Plated
=、SPECIFICATION:
1.Current Rating:3 AMPS
2.Insulation Resistance: 100M Ω MIN. At 500VDC
3.Dielectric Strength: 500V for One minute
4.Operation Temperature: -55 $^{\circ}$ C~+105 $^{\circ}$ C.
*【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®	
DIM. x. x.x x.xx		TOL. ±0.30 ±0.25 ±0.05		TITLE: DP-9M 柳鱼叉锁9.6螺丝				
GENERAL ANGLE: x. x.x x.xx		±5.0° ±2.0° ±1.0°						
		DWG. NO.: D-USB-DS1034-09M		CHECKED: MAX				
		PART NO.: D-USB-DS1034-09M		DRAWN: ELLA				
		UNIT: mm		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4		