








REV.	Q'TY	ECN. NO.	APR.	DATE



Technical requirements	
Characteristic impedance	50Ω
Frequency range	0-6GHZ
Contact resistance	
Inner conductor	<3mΩ
Outer conductor	<2mΩ
Insulated resistance	>5000MΩ
Salt spray time	48H
Separation force	>0.28N
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	



PCB.WELDING DRAWING (TOLERANCE:±0.05)



1	半螺铜座	1	黄铜	镀金
2	尖头焊针	1	黄铜	镀金
3	绝缘体	1	PTFE	
序号	名称	数量	材料	备注

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 正牌-半螺铜座-H13.5-L5.3-J	
.X±0.35	X.*± 5'	CHK.	Jack	DWG NO. XY-SMA-KE	
.XX±0.25	.X.*± 1	DRA.	Can	PROJ. CUSTOMER DRAWING	
.XXX±0.15	.XX.*±	SIZE	A4	SCALE	1:1
			SHEET	1/1	REV. A