





芯数	A	B	C
2	2.0	8.0	4.8
3	4.0	10.0	6.8
4	6.0	12.0	8.8
5	8.0	14.0	10.8
6	10.0	16.0	12.8
7	12.0	18.0	14.8
8	14.0	20.0	16.8
9	16.0	22.0	18.8
10	18.0	24.0	20.8
11	20.0	26.0	22.8
12	22.0	28.0	24.8
13	24.0	30.0	26.8
14	26.0	32.0	28.8
15	28.0	34.0	30.8
16	30.0	36.0	32.8



塑胶 LCP, 米色
插针 黄铜, 镀锡
焊片 黄铜, 镀锡



		深圳市虹成电子有限公司		品 名 TITLE	针座	
				料 号 PART NO	HC-HY2.0-7PWT	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1 : 1			
X.±0.30	X.±5°	单 位 UNIT	MM			
.X±0.25	.X±3°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
.XX±0.20	.XX±1°	版 本 REV	A	批 准 APPROVE	赵亮亮	