









7	8	9
标记 MARK	ECN编号/变更内容 ECN NO./DEFINITION	修改 REVISE
		日期 DATE
		核准 APPROVE

No. of Contacts	DIM A	DIM B	DIM C
2	1.25	3.85	5.75
3	2.50	5.10	7.00
4	3.75	6.35	8.25
5	5.00	7.60	9.50
6	6.25	8.85	10.75
7	7.50	10.10	12.00
8	8.75	11.35	13.25
9	10.00	12.60	14.50
10	11.25	13.85	15.75
11	12.50	15.10	17.00
12	13.75	16.35	18.25
13	15.00	17.60	19.50
14	16.25	18.85	20.75
15	17.50	20.10	22.00
16	18.75	21.35	23.25




PCB Layout


技术要求:  
 额定电流: 1.0A AC,DC  
 (注: AWG32# 0.8)  
 额定电压: 50V AC  
 温度范围: -25°C~85°C  
 接触电阻: ≤0.02Ω  
 绝缘电阻: ≥100MΩ  
 耐压: 500V AC/min  
 材料:  
 塑胶 LCP,米色  
 金属 铜合金,镀锡




2PIN~6PIN




7PIN



8PIN~11PIN




12PIN~13PIN



14PIN~16PIN

2	插针	铜	镀锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注


 深圳市虹成电子有限公司  
 品名 TITLE 针座  
 料号 PART NO HC-GH1.25-10PLT

GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE 1:1		
X.±0.30	X.±5°	单位 UNIT MM	制图 DRAW AhYe	
.X±0.25	.X±3°	张数 PART NO 1 OF 1	审核 CHECKED 夏操云	
.XX±0.20	.XX±1°	版本 REV A	批准 APPROVE 赵亮亮	