

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN

尺寸 (mm)

A

B

02P

4.20

9.60

03P

8.40

13.80

04P

12.60

18.00

05P





16.80

22.20

06P



21.00

26.40



SPECIFICATIONS

- 1.Current Rating:7A AC, DC
- 2.Voltage Rating:600V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material: Wafer PA66
PIN Brass Tin-plated



1	胶壳	PA66	本色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	胶壳	
			料号 PART NO	HC-JK-5557-5Y	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
X±0.25 X±1°		单位 UNIT	MM	制图 DRAW	AhYe
.X±0.20 .X°±1°		张数 PART NO	1 OF 1	审核 CHECKED	夏操云
.XX±0.15 .XX°±0.5°		版本 REV	A	批准 APPROVE	赵亮亮
.XXX±0.10 .XXX°±0.5°					