

标 记 MARK	ECN编号/变更内容 ECN_NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编号

尺寸 (mm)

A

B

2A

2.50

7.50

3A

5.00

10.00

4A

7.50

12.50

5A

10.00

15.00

6A

12.50

17.50

7A

15.00

20.00

8A

17.50

22.50

9A

20.00

25.00

10A

22.50

27.50

11A

25.00

30.00





12A

27.50

32.50

SPECIFICATIONS

- 1.Current Rating:3A AC, DC
2.Voltage Rating:250V AC, DC
3.Temperatuer Range:−25℃~+85℃
4.Contact Resistance:20mΩ Max
5.Insulation Resistance:1000MΩ Min
6.Withstanding Voltang:800V AC/minute
7.Material:Wafer Nylon66
PIN Brass Tin-plated



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	PA66	白色	
序 号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-EH2.54-2A-TW

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比 列
SCALE

1:1



X±0.25 X'±2"

单 位
UNIT

MM

制 图
DRAW

AhYe

.X±0.20 X'±1"

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

.XX±0.15 .XX'±0.5"

版 本
REV

A

批 准
APPROVE

赵亮亮

.XXX±0.10 .XXX'±0.5"

