








规格说明: Specifications:

电气特性: Electrical:

- 1.额定电流: Current Rating
1.0A/contact terminal
- 2.额定电压: Voltage Rating 30V DC
- 3.接触电阻: Contact Resistance 50 milliohms MAX
- 4.耐电压: Dielectric Withstanding Voltage: 300 V AC AT Sea Level
- 5.绝缘电阻: Insulation Resistance: 100MEGA ohms MIN

原材料: Raw material:

- 1.塑胶: Plastic cement:
High Temperature Thermoplastics,
LCP Black
 - 2.端子: Contact: Copper Alloy C2680/C5191
 - 3.外壳: Shell: SPCC/Copper Alloy C2680
- 电镀: Electroplate:
- 1.端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails
 - 2.外壳: Shell:
Nickel Plating

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd						
TOLERANCE UNLESS OTHERWISE SPECIFIED								
.X±0.35	X.*± 5°	APR. Alex	TITLE: MINI USB 5P/F SMT B#(0.3T, 0.6#)					
.XX±0.25	.X.*± 3°	CHK. Jack	DWG NO. XY-U-M-M5SS-W-2					
.XXX±0.15	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING			
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		