

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

编号

尺寸 (mm)

A

B

2X01

4.20

5.60

2X02

8.40

9.80

2X03

12.60

14.00

2X04

16.80

18.20

2X05

21.00

22.40

2X06

25.20

26.60

2X07

29.40

30.80

2X08

33.60

35.00

2X09

37.80

39.20

2X10

42.00

43.40

2X11





46.20

47.60

2X12


46.20

52.30



SPECIFICATIONS

- 1.Current Rating: 7A AC, DC
- 2.Voltage Rating: 600V AC, DC
- 3.Temperatuer Range: -25℃~+85℃
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material: Wafer PA66
PIN Brass Tin-plated



1	胶壳	PA66	本色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	胶壳	
			料号 PART NO	HC-JK-5557-2x10Y	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
X±0.25	X'±2"	单位 UNIT	MM	制图 DRAW	AhYe
.X±0.20	.X'±1"	张数 PART NO	1 OF 1	审核 CHECKED	夏操云
.XX±0.15	.XX'±0.5"	版本 REV	A	批准 APPROVE	赵亮亮
.XXX±0.10	.XXX'±0.5"				