

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

PIN	尺寸 (mm)	
	A	B
2*04AW	7.50	15.00
2*05AW	10.00	17.50
2*06AW	12.50	20.00
2*07AW	15.00	22.50
2*08AW	17.50	25.00
2*09AW	20.00	27.50
2*10AW	22.50	30.00
2*11AW	25.00	32.50
2*12AW	27.50	35.00
2*13AW	30.00	37.50
2*14AW	32.50	40.00
2*15AW	35.00	42.50

A

B

C

D

E

F

G

A

B



C

D

E

F

G



SPECIFICATIONS

1.Current Rating:1A AC, DC

2.Voltage Rating: 30V AC, DC

3.Temperatuer Range: -25°C~+85°C



4.Contact Resistance: 30mΩ Max

5.Insulation Resistance: 100MΩ Min

6.Withstanding Voltang: 200V AC/minute


7.Material: Wafer PA66

PIN C2680 Tin-plated



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	PA66	米色	
序号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE	针座	
		料 号 PART NO	HC-XA2.54-2X5AW	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
X.X±0.25	X.*±2°	单 位 UNIT	MM	制 图 DRAW
X.XX±0.20		张 数 PART NO	1 OF 1	审 核 CHECKED
X.XXX±0.10		版 本 REV	A	批 准 APPROVE
				夏操云
				赵亮亮

