









P.C.B LAYOUT



SCHEMATIC



6	圆针	1	黄铜棒	亮锡
5	平片	1	H62黄铜带(Y)T=0.35	亮锡
4	弯片	1	H62黄铜带(Y)T=0.3	亮锡
3	簧片	1	磷铜带T=0.25	亮锡
2	后盖	1	PA9T	黑色
1	底座	1	PA9T	黑色
序号	名称	数量	材料	备注

Main technical performance

Rated electrical loadDC 24V 3A

Temperature-30℃~+70℃

Insulation resistance≥100MΩ

Contact Resistance≤0.3Ω

Pressure resistanceAC500V(50Hz)/min

Insertion force3-20N

service life5000cycles

DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

.X±0.2X.*±1

.XX±0.1X.*±0.5

.XXX±0.05XX.*±

APR. Alex

CHK. Jack

DRA. Can

TITLE: DC SOCKET

DWG NO. XY-DC050-T2.0

PROJ. 

SIZE A4

SCALE 1:1

CUSTOMER DRAWING

SHEET 1/1

REV. A