

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN

尺寸 (mm)

A

B

02P

4.20

9.60

03P

8.40

13.80

04P

12.60

18.00

05P





16.80

22.20

06P



21.00

26.40



SPECIFICATIONS

- 1.Current Rating:7A AC, DC
- 2.Voltage Rating:600V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material: Wafer PA66
PIN Brass Tin-plated



1	胶壳	PA66	本色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	胶壳
料号 PART NO	HC-JK-5557-2Y

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

X±0.25 X±1°

单 位
UNIT

MM

X±0.20 X±1°

张 数
PART NO

1 OF 1

.XX±0.15 .XX°±0.5°

审 核
CHECKED

夏操云

.XXX±0.10 .XXX°±0.5°

版 本
REV

A

批 准
APPROVE

赵亮亮

