

尺寸 (mm)4.4






10

1

1

7

1



SPECIFICATIONS

- 1.Current Rating:5A AC, DC
- 2.Voltage Rating:250V AC, DC
- 3.Temperatuer Range:−25°C~+85°C
- 4.Contact Resistance:20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material:Wafer PA66 Black
PIN Brass Tin-plated



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-5557-MX3.0-2x7A

GENERAL TOLERANCES (UNLESS SPECIFIED)		比例 SCALE	1:1	PART NO.			
.X±0.25	.X±2°	单位 UNIT	MM	制图 DRAW	AhYe		
.X±0.25	.X±1°	张数 PART NO	1 OF 1	审核 CHECKED	夏操云		
.XX±0.15	.XX±0.5°	版本 REV	A	批准 APPROVE	赵亮亮		
.XXX±0.10	.XXX±0.5°						

