







SECTION A-A



LOCK CONFIGURATION(锁扣位置)




Part No	CKT	A	B	C
BX-MX1.25-2PWZ-BD	2	1.25	3.20	4.30
BX-MX1.25-3PWZ-BD	3	2.50	4.45	5.55
BX-MX1.25-4PWZ-BD	4	3.75	5.70	6.80
BX-MX1.25-5PWZ-BD	5	5.00	6.95	8.05
BX-MX1.25-6PWZ-BD	6	6.25	8.20	9.30
BX-MX1.25-7PWZ-BD	7	7.50	9.45	10.55
BX-MX1.25-8PWZ-BD	8	8.75	10.70	11.80
BX-MX1.25-9PWZ-BD	9	10.00	11.95	13.05
BX-MX1.25-10PWZ-BD	10	11.25	13.20	14.30
BX-MX1.25-11PWZ-BD	11	12.50	14.45	15.55
BX-MX1.25-12PWZ-BD	12	13.75	15.70	16.80
BX-MX1.25-13PWZ-BD	13	15.00	16.95	18.05
BX-MX1.25-14PWZ-BD	14	16.25	18.20	19.30
BX-MX1.25-15PWZ-BD	15	17.50	19.45	20.55
BX-MX1.25-16PWZ-BD	16	18.75	20.70	21.80
BX-MX1.25-17PWZ-BD	17	20.00	21.95	23.05
BX-MX1.25-18PWZ-BD	18	21.25	23.20	24.30
BX-MX1.25-19PWZ-BD	19	22.50	24.45	25.55
BX-MX1.25-20PWZ-BD	20	23.75	25.70	26.80



技术指标(Technical Index):


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
2. 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。
(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
3. 温度范围(Temperature range): -25°C~+85°C.
4. 额定电压(Rated voltage): 125V, AC/DC(=等效).
5. 接触电阻(Contact resistance): ≤0.02Ω.
6. 绝缘电阻(Insulation resistance): ≥100MΩ

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-MX1.25-NPWZ-BD	版本 REV.	A
			X.±0.50	±1°						
			.X±0.20		审核 CHECK	EVA	品名 TITLE	1.25 Pitch A型带针WTB	页次 SHEET	1/1
			.XX±0.10		核准 APPROVAL	JADE	客户料号 CUTM.NO.			
					单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)	



制图 DRAWN	變更內容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		
			X.±0.50	±1°	审核 CHECK	EVA		
			.X±0.20		核准 APPROVAL	JADE		
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1

9. 纸箱分小、中、标准型3种规格型号:装箱为整箱(左下包装量)采用标准型纸箱包装,未达到整箱数量以产品量适当采用小型或中型纸箱包装。



CKT	B0	W	F	S
(1.25mm pitch)				
2	4.60	16	7.50	
3	5.85			
4	7.10			
5	8.35			
6	9.60			
7	10.85	24	11.50	
8	12.10			
9	13.35			
10	14.60			
11	15.85			
12	17.10	32	14.2±0.10	28.45
13	18.35			
14	19.60			
15	20.85			
16	22.10			
17	23.35			
18	25.85	44	20.2±0.15	40.45
19	28.35			
20	30.85			



Bossie (博锡)