





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

SPECIFICATIONS


- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material:Phosphoric bronze Tin-plated
- 8.Applicable Wire Sizes: AWG#22~38#



SEC: A-A



SEC: B-B



SEC: C-C

1	端子	铜	镀锡	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	端子
料号 PART NO	HC-DZ-XA2. 54-S

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



X.±0.25	X.*±2°
.X±0.25	.X*±1°
.XX±0.15	.XX*±0.5°
.XXX±0.10	.XXX*±0.5°

单位 UNIT	MM
张数 PART NO	1 OF 1
版本 REV	A

制图 DRAW	AhYe
审核 CHECKED	夏操云
批准 APPROVE	赵亮亮

