

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编号

尺寸 (mm)

A

B

	A	B
2X04A	7.50	15.00
2X05A	10.00	17.50
2X06A	12.50	20.00
2X07A	15.00	22.50
2X08A	17.50	25.00
2X09A	20.00	27.50
2X10A	22.50	30.00
2X11A	25.00	32.50
2X12A	27.50	25.00
2X13A	30.00	37.50
2X14A	32.50	40.00

A

B

C

D

E

F

G

A

B





C

D

E



F

G




SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25℃~+85℃
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Wafer Nylon66
PIN Brass Tin-plated



2	插针	铜	镀锡	
1	基座	PA66	米色	
序 号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE	针座	
		料 号 PART NO	HC-XA2.54-2x5A	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
X±0.25	X'±2'	单 位 UNIT	MM	制 图 DRAW
.X±0.20	.X'±1'	张 数 PART NO	1 OF 1	审 核 CHECKED
.XX±0.15	.XX'±0.5'	版 本 REV	A	批 准 APPROVE
.XXX±0.10	.XXX'±0.5'			夏操云 赵亮亮

