








标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

PIN	尺寸 (mm)			
	A	B	C	D
02	0.80	3.04	3.80	1.90
03	1.60	3.84	4.60	2.70
04	2.40	4.64	5.40	3.50
05	3.20	5.44	6.20	4.30
06	4.00	6.24	7.00	5.10
07	4.80	7.04	7.80	5.90
08	5.60	7.84	8.60	6.70
09	6.40	8.64	9.40	7.50
10	7.20	9.44	10.2	8.30



PCB Layout

技术要求:

额定电流: 0.7A AC,DC

额定电压: 30V AC

温度范围: -40° C~+85° C

接触电阻: ≤0.03 Ω

绝缘电阻: ≥100M Ω

耐 压: 200V AC/min

2	接触	铜	镀锡	
1	基座	LCP	米色	
序号	品 名	材 质	电镀/颜色	备注



深圳市虹成电子有限公司

品 名 TITLE		针座		
料 号 PART NO		HC-SURO. 8-2PLT		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
X.±0.30	X.±5°	单 位 UNIT	MM	制 图 DRAW
.X±0.25	.X±3°	张 数 PART NO	1 OF 1	审 核 CHECKED
.XX±0.20	.XX±1°	版 本 REV	A	批 准 APPROVE

AhYe

夏操云

赵亮亮

