








序号	品名	材质
①	ZH1.5弯针WTB胶芯	LCP UL94V-0 本色
②	ZH1.5弯针WTB端子	铜合金/表面镀锡






制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	审核 CHECK	批准 APPROVAL	单位 UNITS	比例 SCALE	1:1
			X.±0.50	±1°						
			.X±0.20							
			.XX±0.10							

Part No	CKT	A	B
BX-ZH1.5-2PWZ-BD	2	1.5	4.5
BX-ZH1.5-3PWZ-BD	3	3.0	6.0
BX-ZH1.5-4PWZ-BD	4	4.5	7.5
BX-ZH1.5-5PWZ-BD	5	6.0	9.0
BX-ZH1.5-6PWZ-BD	6	7.5	10.5
BX-ZH1.5-7PWZ-BD	7	9.0	12.0
BX-ZH1.5-8PWZ-BD	8	10.5	13.5
BX-ZH1.5-9PWZ-BD	9	12.0	15.0
BX-ZH1.5-10PWZ-BD	10	13.5	16.5
BX-ZH1.5-11PWZ-BD	11	15.0	18.0
BX-ZH1.5-12PWZ-BD	12	16.5	19.5
BX-ZH1.5-13PWZ-BD	13	18.0	21.0
BX-ZH1.5-14PWZ-BD	14	19.5	22.5
BX-ZH1.5-15PWZ-BD	15	21.0	24.0
BX-ZH1.5-16PWZ-BD	16	22.5	25.5
BX-ZH1.5-17PWZ-BD	17	24.0	27.0
BX-ZH1.5-18PWZ-BD	18	25.5	28.5
BX-ZH1.5-19PWZ-BD	19	27.0	30.0
BX-ZH1.5-20PWZ-BD	20	28.5	31.5

技术指标(Technical Index):



- 1.温度范围(Temperature range):-25℃~+85℃.
- 2.额定电压(Rated voltage):100V,AC.
- 3.额定电流(Rated current):1.0A AC,DC.
- 4.接触电阻(Contact resistance):<20mΩ .
- 5.绝缘电阻(Insulation resistance):≥500MΩ.
- 6.耐压值(Withstanding voltage):500V AC/minute.

料号 PART NO.	BX-ZH1.5-NPWZ-BD	版本 REV.	A
品名 TITLE	ZH1.5弯针WTB	页次 SHEET	1/1
客户料号 CUTM.NO.			



NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$. (10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm. (载带拱/弧形MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS. (所有的尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING. (载带材料: 透明防静电 PS, 冷封.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.40 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 8.832 METERS. (每卷包装长度: 8.832米.)
- 7.COMPONENT LOAD PER REEL: 700 PCS. (每卷包装数量: 700只, 前后各空18只.)
- 8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保龙填充.
- 9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.



纸箱型号	小型	中型	标准型
Carton Type	Small Size	Medium	Standard
高度	7.5	15	32
Hight (CM)			

CKT (1.5mm pitch)	B0	W	F	S
2	4.80	16	7.50	
3	6.30			
4	7.80			
5	9.30			
6	10.80			
7	12.30	24	11.50	
8	13.80			
9	15.30			
10	16.80			
11	18.30	32	14.20±0.10	28.40
12	19.80			
13	21.30			
14	22.80			
15	24.30			
16	25.80			
17	27.30	44	20.20±0.10	40.40
18	28.80			
19	30.30			
20	31.80			

CKT (1.5mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	16	700	14	9800
3				
4				
5				
6				
7	24	700	10	7000
8				
9				
10				
11	32	700	8	5600
12				
13				
14				
15				
16				
17	44	700	6	4200
18				
19				
20				

制图	变更内容	日期	GENERAL TOLERANCE	制图	EMMA	料号	BX-ZH1.5-NPWZ-BD	版本	A
DRAWN	DESCRIPTION	DATE	X.±0.50	±2°	DRAWING	品名	ZH1.5弯针WTB载带包装	REV.	1/1
			.X±0.25		审核	CHECK	客户料号	SHEET	
			.XX±0.15		核准	APPROVAL	CUTM.NO.		
					单位	MM	比例	SCALE	1:1

Bossie (博锡)