







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN

尺寸 (mm)

PIN	尺寸 (mm)		
	A	B	C
02	1.00	4.50	2.50
03	2.00	5.50	3.50
04	3.00	6.50	4.50
05	4.00	7.50	5.50
06	5.00	8.50	6.50
07	6.00	9.50	7.50
08	7.00	10.50	8.50
09	8.00	11.50	9.50
10	9.00	12.50	10.50
11	10.00	13.50	11.50
12	11.00	14.50	12.50
13	12.00	15.50	13.50
14	13.00	16.50	14.50
15	14.00	17.50	15.50
16	15.00	18.50	16.50

技术要求:

额定电流: 1.0A AC,DC
(使用AWG#28时适用)

额定电压: 50V (AC,DC)

温度范围: -25° C~+85° C

接触电阻: ≤20mΩ

绝缘电阻: ≥100MΩ

耐 压: 500V AC/min

适用导线规格: AWG#28~#32

2	接触	铜	镀锡	
1	基座	LCP	米色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-SHB1.0-2PLT

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 列
SCALE

1:1

X.±0.2
.X±0.1
.XX±0.05X.±5°
.X±3°
.XX±1°单 位
UNIT
张 数
PART NO
版 本
REVMM
1 OF 1
A制 图
DRAW
审 核
CHECKED
批 准
APPROVEAhYe
夏操云
赵亮亮