





标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编号	尺寸 (mm)	
	A	B
02Y	2. 50	6. 80
03Y	5. 00	9. 30
04Y	7. 50	11. 80
05Y	10. 00	14. 30
06Y	12. 50	16. 80
07Y	15. 00	19. 30
08Y	17. 50	21. 80
09Y	20. 00	24. 30
10Y	22. 50	26. 80
11Y	25. 00	29. 30
12Y	27. 50	31. 80
13Y	30. 00	34. 30
14Y	32. 50	36. 80
15Y	35. 00	39. 30
16Y	37. 50	41. 80

SPECIFICATIONS
1.Current Rating: 3A AC, DC
2.Voltage Rating: 250V AC, DC
3.Temperatuer Range: -25℃~+85℃
4.Contact Resistance: 20mΩ Max
5.Insulation Resistance: 1000MΩ Min
6.Withstanding Voltang: 1000V AC/minute
7.Material: Housing: PA66

1	外壳	PA66	本色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	胶壳	
			料 号 PART NO	HC-XHB2. 54-5Y	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.±0.25	X.*±2°	单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.20	.X*±1°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15	.XX*±0.5°	版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10	.XXX*±0.5°				