



标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE




PIN	A	B	C
02AW	2.50	7.50	6.80
03AW	5.00	10.00	9.30
04AW	7.50	12.50	11.80
05AW	10.00	15.00	14.30
06AW	12.50	17.50	16.80
07AW	15.00	20.00	19.30
08AW	17.50	22.50	21.80
09AW	20.00	25.00	24.30
10AW	22.50	27.50	26.80
11AW	25.00	30.00	29.30
12AW	27.50	32.50	31.80
13AW	30.00	35.00	34.30
14AW	32.50	37.50	36.80



Circuit 1



6.00±0.20



PCB LAYOUT

SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material: Wafer PA66,
PIN Brass Tin-plated

2	插针	铜	镀锡	
1	基座	PA66	白色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品 名 TITLE	针座	
			料 号 PART NO	HC-EH2. 54-6AW-TW	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.±0.25	X.*2"	单 位 UNIT	MM	制 图 DRAW	AhYe
.X*±0.25	.X*±1"	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15	.XX*±0.5"	版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10	.XXX*±0.5"				