




标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE




No. of Contacts	DIM A	DIM B	DIM C
2	2.5	5.7	3.0
3	5.0	8.2	4.0
4	7.5	10.7	5.0
5	10.0	13.2	7.5
6	12.5	15.7	10.0
7	15.0	18.2	12.5
8	17.5	20.7	12.5
9	20.0	23.2	12.5
10	22.5	25.7	12.5
11	25.0	28.2	12.5
12	27.5	30.7	12.5
13	30.0	33.2	12.5
14	32.5	35.7	12.5
15	35.0	38.2	12.5
16	37.5	40.7	12.5



2PIN



3PIN



技术要求:

额定电流: 3.0A AC,DC

额定电压: 250V AC,DC

温度范围: -25°C~85°C

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ

耐 压: 1000V/min

材 料: PA66, 白色

1	胶壳	PA66	白色	
序号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	胶壳
料 号 PART NO	HC-XHB2. 54-8Y-L

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 列
SCALE

1:1



X.±0.30	X.±5°
.X±0.25	.X±3°
.XX±0.20	.XX±1°

单 位 UNIT	MM
张 数 PART NO	1 OF 1
版 本 REV	A

制 图 DRAW	AhYe
审 核 CHECKED	夏操云
批 准 APPROVE	赵亮亮

