










标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
-------------	---------------------------------	---------------	-------------	----------------

PIN	尺寸 (mm)		
	A	B	C
02	1.00	4.50	2.50
03	2.00	5.50	3.50
04	3.00	6.50	4.50
05	4.00	7.50	5.50
06	5.00	8.50	6.50
07	6.00	9.50	7.50
08	7.00	10.50	8.50
09	8.00	11.50	9.50
10	9.00	12.50	10.50
11	10.00	13.50	11.50
12	11.00	14.50	12.50
13	12.00	15.50	13.50
14	13.00	16.50	14.50
15	14.00	17.50	15.50
16	15.00	18.50	16.50

技术要求:

额定电流: 1.0A AC,DC
(使用AWG#28时适用)

额定电压: 50V (AC,DC)

温度范围: -25° C~+85° C

接触电阻: ≤20mΩ

绝缘电阻: ≥100MΩ

耐 压: 500V AC/min

适用导线规格: AWG#28~#32

2	接触	铜	镀锡	
1	基座	LCP	米色	
序号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE	针座	
		料 号 PART NO	HC-SHB1.0-5PLT	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
X.±0.2	X.±5°	单 位 UNIT	MM	
.X±0.1	.X±3°	张 数 PART NO	1 OF 1	审 核 CHECKED
.XX±0.05	.XX±1°	版 本 REV	A	批 准 APPROVE
		制 图 DRAW	AhYe	夏操云
		审 核 CHECKED	赵亮亮	

