







技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC, DC
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$



Part No	CKT	A	B	C	D
BX-NH1.0-2PLT-BD	2	1.00	2.52	4.00	3.00
BX-NH1.0-3PLT-BD	3	2.00	3.52	5.00	4.00
BX-NH1.0-4PLT-BD	4	3.00	4.52	6.00	5.00
BX-NH1.0-5PLT-BD	5	4.00	5.52	7.00	6.00
BX-NH1.0-6PLT-BD	6	5.00	6.52	8.00	7.00
BX-NH1.0-7PLT-BD	7	6.00	7.52	9.00	8.00
BX-NH1.0-8PLT-BD	8	7.00	8.52	10.00	9.00
BX-NH1.0-9PLT-BD	9	8.00	9.52	11.00	10.00
BX-NH1.0-10PLT-BD	10	9.00	10.52	12.00	11.00
BX-NH1.0-11PLT-BD	11	10.00	11.52	13.00	12.00
BX-NH1.0-12PLT-BD	12	11.00	12.52	14.00	13.00
BX-NH1.0-13PLT-BD	13	12.00	13.52	15.00	14.00
BX-NH1.0-14PLT-BD	14	13.00	14.52	16.00	15.00
BX-NH1.0-15PLT-BD	15	14.00	15.52	17.00	16.00
BX-NH1.0-16PLT-BD	16	15.00	16.52	18.00	17.00

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.		版本 REV.	A
①	1.0-B型立式WTB胶芯	PA10T UL94V-0米白色				X.±0.50	±1°		品名 TITLE	BX-NH1.0-NPLT-BD	页次 SHEET	1/1
②	1.0-B型立式WTB端子	铜合金/表面镀锡				.X±0.20		审核 CHECK	客户料号 CUTM.NO.			
③	1.0-B型立式WTB焊片	铜合金/表面镀锡				.XX±0.10		核准 APPROVAL				
④	1.0-B型立式WTB吸盖	LCP UL94V-0 本色						单位 UNITS				
								MM 比例 SCALE	1:1			