

NOTES:

1.) MATERIAL:

1-1. HOUSING: LCP, UL 94V-0, COLOR: BLACK;

1-2. CONTACT: C2680 T=0.20;

1-3. SHELL: SPCC, T=0.50;

2.) FINISH:

2-1. CONTACT: Au G/F PLATING ON CONTACT AREA, (SEE P/N DESCRIBING) MATTE PURE Sn 50u" Min. PLATING ON SOLDER TAILS

2-2. SHELL: PLATING Ni 50u Min

3.) SPECIFICATIONS:

3-1. VOLTAGE RATING: 40V

3-2. CURRENT RATING: 0.5A





3-3. INSULATION RESISTANCE: 100MEG.OHM MIN

3-4. CONTACT RESISTANCE: 10 MILL.OHM MAX

3-5. OPERATION TEMPERATURE: -20°C TO +85°C


3-6. INSERT FORCE: 44.1N MAX

3-7. EXTRACT FORCE: 9.8~39.2N




RECOMMENDED PCB LAYOUT (T:1.60mm)

TOLERANCE UNSPECIFIED ±0.10mm




DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR. Alex	TITLE: HDMI		
.XX±0.25	.X*± 3°	CHK. Jack	DWG NO. HDMI-19PIN-A		
.XXX±0.15	.XX*± 1°	DRA. Can	PROJ. 	CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1 / 1

REV.	Q'TY	ECN. NO.	APR.	DATE



客户使用出料方向

PCS/卷	卷/箱	PCS/箱
480	10	4800




标签

10卷


防水袋

四周角落填充三角垫

纸箱内上下各垫一层纸板



31 CM



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.35	X.*± 5°	APR.	Alex	TITLE: HDMI接口连接器			
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. HDMI-19PIN-A			
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A