






标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

| PIN  | A     | B     | C     |
|------|-------|-------|-------|
| 02AW | 2.50  | 7.50  | 6.80  |
| 03AW | 5.00  | 10.00 | 9.30  |
| 04AW | 7.50  | 12.50 | 11.80 |
| 05AW | 10.00 | 15.00 | 14.30 |
| 06AW | 12.50 | 17.50 | 16.80 |
| 07AW | 15.00 | 20.00 | 19.30 |
| 08AW | 17.50 | 22.50 | 21.80 |
| 09AW | 20.00 | 25.00 | 24.30 |
| 10AW | 22.50 | 27.50 | 26.80 |
| 11AW | 25.00 | 30.00 | 29.30 |
| 12AW | 27.50 | 32.50 | 31.80 |
| 13AW | 30.00 | 35.00 | 34.30 |
| 14AW | 32.50 | 37.50 | 36.80 |



Circuit 1



PCB LAYOUT

## SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material: Wafer PA66,  
PIN Brass Tin-plated

|    |    |      |       |    |
|----|----|------|-------|----|
| 2  | 插针 | 铜    | 镀锡    |    |
| 1  | 基座 | PA66 | 白色    |    |
| 序号 | 品名 | 材质   | 电镀/颜色 | 备注 |

|                                                                                       |             |                                                                                       |                |                                                                                       |      |
|---------------------------------------------------------------------------------------|-------------|---------------------------------------------------------------------------------------|----------------|---------------------------------------------------------------------------------------|------|
|  | 深圳市虹成电子有限公司 |                                                                                       | 品 名<br>TITLE   | 针座                                                                                    |      |
|                                                                                       |             |                                                                                       | 料 号<br>PART NO | HC-EH2. 54-3AW-TW                                                                     |      |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                              |             | 比 列<br>SCALE                                                                          | 1:1            |  |      |
| X.±0.25                                                                               | X.*2"       | 单 位<br>UNIT                                                                           | MM             | 制 图<br>DRAW                                                                           | AhYe |
| .X*±0.25                                                                              | .X*±1"      | 张 数<br>PART NO                                                                        | 1 OF 1         | 审 核<br>CHECKED                                                                        | 夏操云  |
| .XX±0.15                                                                              | .XX*±0.5"   | 版 本<br>REV                                                                            | A              | 批 准<br>APPROVE                                                                        | 赵亮亮  |
| .XXX±0.10                                                                             | .XXX*±0.5"  |  |                |                                                                                       |      |