





SPECIFICATIONS

- Current Rating: 4A AC, DC
- Voltage Rating: 250V AC, DC
- Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- Contact Resistance: $20\text{m}\Omega$ Max
- Insulation Resistance: $1000\text{M}\Omega$ Min
- Withstanding Voltage: 1000V AC/minute
- Material: Phosphoric bronze Tin-plated
- Applicable Wire Sizes: AWG#24~30#

1	端子	铜	镀锡	
序号	品名	材质	电镀/颜色	备注
 深圳市虹成电子有限公司		品名 TITLE	端子	
		料号 PART NO	HC-DZ-XH2510	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比例 SCALE	1:1	
X $\pm$ 0.25	X' $\pm$ 2'	单位 UNIT	MM	制图 DRAW
.X $\pm$ 0.20	.X' $\pm$ 1'	张数 PART NO	1 OF 1	审核 CHECKED
.XX $\pm$ 0.15	.XX' $\pm$ 0.5'	版本 REV	A	批准 APPROVE
.XXX $\pm$ 0.10	.XXX' $\pm$ 0.5'			夏操云
				赵亮亮

