

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

芯数	A	B	C
2	2.0	8.0	4.8
3	4.0	10.0	6.8
4	6.0	12.0	8.8
5	8.0	14.0	10.8
6	10.0	16.0	12.8
7	12.0	18.0	14.8
8	14.0	20.0	16.8
9	16.0	22.0	18.8
10	18.0	24.0	20.8
11	20.0	26.0	22.8
12	22.0	28.0	24.8
13	24.0	30.0	26.8
14	26.0	32.0	28.8
15	28.0	34.0	30.8
16	30.0	36.0	32.8

A

B





C

D

E

F

G



技术要求:

额定电流: 2.0A AC,DC

额定电压: 250V AC,DC

温度范围: -25°C~85°C

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ


耐 压: 800V/min

材 料:

塑胶 LCP,米色

插针 黄铜,镀锡

焊片 黄铜,镀锡

PCB LAYOUT
TOL.: ±0.05

2	插针	铜	镀锡	
1	基座	LCP	米色	
序 号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-HY2. 0-3PWT

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 列
SCALE

1:1



X.±0.30	X.±5°
.X±0.25	.X±3°
.XX±0.20	.XX±1°

单 位 UNIT	MM
张 数 PART NO	1 OF 1
版 本 REV	A

制 图 DRAW	AhYe
审 核 CHECKED	夏操云
批 准 APPROVE	赵亮亮

