










PCB WELDING DRAWING (TOLERANCE: ±0.05)


5	銅片	1	黃銅片	鍍銀
4	蓋片	1	H62黃銅(Y)	鍍銀
3	簧片	1	磷銅	鍍銀
2	屏蔽罩	1	H62黃銅(Y)	鍍銀
1	底座	1	PPA	鍍銀
序號	名稱	數量	材料	備註

Main technical performance

Rated electrical load	DC 24V 8A
Contact resistance	≤0.03Ω
Insulation resistance	>100MΩ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-40℃~+85℃
service life	5000cycles



RECOMMEND PULG



SCHEMATIC

DIMENSION IN mm

TOLERANCE UNLESS OTHERWISE SPECIFIED

.X±0.3	X.*±1
.XX±0.25	.X.*±0.5
.XXX±0.15	.XX.*±

厦门市辛译精密电子有限公司
Xiamen XinYi Xyecom Electronics Co.,Ltd

APR.	Alex
CHK.	Jack
DRA.	Can

TITLE: DC SOCKET

DWG NO. XY-DC007B-2.0

PROJ.

CUSTOMER DRAWING

SIZE A4

SCALE 1:1

SHEET 1/1

REV. A