

NOTES:

1.Specification:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30° to $+85^{\circ}$.
- 3>.Storage Temperature: -40° to $+85^{\circ}$.
- 4>.Mechanical Life: 1000 cycles operations.
- 5>.Resistance to Soldering: $260\pm 5^{\circ}$ for 3-5 Seconds.

2.PLATING:

- 1>.GOLD flash 1u"(min) SOLDERTAIL,
3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>.Non-switch Rating: 100mA at 50V DC.
- 2>.Switching Rating: 25mA at 24V DC.
- 3>.Contact Resistance: Inital 50m Ω Max.
Contact Resistance: After life 100m Ω Max.
- 4>.Insulation Resistance: 100M Ω Min at 100VDC.
- 5>.Dielectric Strength: 300V AC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

XY-DSHP XX I S-R

(包装方式: T=Tub R=Reel)





(封装型: S=贴片 / D=插件 / J型)

(L=高柄 / S=低柄 / T=低柄贴片)


(开关位数: 02位-----10位)

5.PACKING: 2000pcs/Reel/Box.

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: PRODUCT Family DSHP Series Pitch 1.27mm	
.X ± 0.35	X.* $\pm 5^{\circ}$	CHK.	Jack	DWG NO. XY-DSHP06TS-R	
.XX ± 0.25	.X.* $\pm 3^{\circ}$	PROJ.		CUSTOMER DRAWING	
.XXX ± 0.15	.XX.* $\pm 1^{\circ}$	DRA.	Can	SIZE A4	SCALE 1:1
				SHEET 1/1	REV. A



[Schematic]



[P.C.B.LAYOUT]