

NOTES:

1.Specification:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30°C to $+85^{\circ}\text{C}$.
- 3>.Storage Temperature: -40°C to $+85^{\circ}\text{C}$.
- 4>.Mechanical Life: 1000 cycles operations.
- 5>.Resistance to Soldering: $260\pm 5^{\circ}\text{C}$ for 3-5 Seconds.

2.PLATING:

- 1>.GOLD flash $1\mu\text{m}$ (min) SOLDERTAIL,
 $3\mu\text{m}$ GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>.Non-switch Rating: 100mA at 50V DC.
- 2>.Switching Rating: 25mA at 24V DC.
- 3>.Contact Resistance: Initial $50\text{m}\Omega$ Max.
Contact Resistance: After life $100\text{m}\Omega$ Max.
- 4>.Insulation Resistance: $100\text{M}\Omega$ Min at 100VDC.
- 5>.Dielectric Strength: 300V AC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

- 5>.PACKING: 2000pcs/Reel/Box.






PART NUMBER DESCRIPTION:

XY-DSHC XX I S- R
(包装方式: T=Tub R=Reel)

(端牌型: S=贴片 / D=插件 / J型)

(L=高插 / S=低插 / T=低插贴片)

(开关位数: 02位-----12位)



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
>0±0.05	>0°±0.5°	APR. Alex	TITLE: PRODUCT Family DSHP Series Pitch 1.27mm		
>1±0.10	>5°±1.0°	CHK. Jack	DWG NO. XY-DSHC04TS-R		
>10±0.30		DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1