







Rohs
环保

A型



PCB Layout Diagram
Top View



REV.	ECN NO.	REVISED	DATE

PCB Layout Diagram									
Top View									
UNLESS OTHERWISE SPECIFIED TOLERANCES					TITLE:				
DECIMALS:		ANGLES:		DSND	YangFeng	DATE	2018-04-09	PART NO.:	
X .X		X .30 X .1		CHKD	ZhouRuicai	DATE	2018-04-09		
X .X		X .X .10.5		APVD	XueShunrong	DATE	2018-04-09		
X .XX		X .XX							
X .XX		X .XX							
X .XXX		X .XX							
X .XXX		X .XX							
WEIGHT: 0.168g									
SCALE: 3:1		SIZE: A4		VIEW: 					
UNIT: mm		REV.: A/0		OBJECT:		DRAW NO.: -CR20-XXX			
SHEET 1 OF 1									
H									

LQ HUANG

1	TERMINAL(+)	1	SPCC T=0.2	Ni-Plating						
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR						
1		2			3	4	5	6	7	8