







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

12-24 CONTACTS



02-11 CONTACTS



MATED CONDITION

PIN

尺寸 (mm)

	A	B	C
02	0.80	1.78	2.40
03	1.60	2.58	3.20
04	2.40	3.38	4.00
05	3.20	4.18	4.80
06	4.00	4.98	5.60
07	4.80	5.78	6.40
08	5.60	6.58	7.20
09	6.40	7.38	8.00
10	7.20	8.18	8.80

技术要求:

额定电流: 0.7A AC,DC

额定电压: 30V AC

温度范围: -40° C~+85° C

接触电阻: ≤0.03 Ω

绝缘电阻: ≥100M Ω

耐 压: 200V AC/min

适用电线: AWG#32

绝缘层直径: $\phi 0.38 \pm 0.02$ mm

2	端子	铜	镀金	
1	胶壳	PA66	白色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	胶壳+端子
料 号 PART NO	HC-SUR0. 8-3YD

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 列
SCALE

1:1

单 位
UNIT

MM

制 图
DRAW审 核
CHECKED批 准
APPROVE

X.±0.30

X.±5°

.X±0.25

.X±3°

.XX±0.20

.XX±1°

张 数
PART NO

1 OF 1

夏 操 云

赵 亮 亮

