




PCB.LAYOUT
TOL:±0.05

备注:

电气性能:

接触阻抗:30毫欧(最大)

绝缘阻抗:1000兆欧(最小)

耐高压:500V AC一分钟

电镀:

端子:接触区域镀金

焊接区镀亮锡100u"Min

外壳:全区域镀镍50u"Min

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.35	X.*± 5°	APR. Alex	TITLE: USB AF 90度 转接器				
.XX±0.25	.X*± 3°	CHK. Jack	DWG NO. XY-AF90-WJDG				
.XXX±0.15	.XX*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING		
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	