










标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Pin	DIM A	DIM B	DIM C	DIM D
2	2.50	7.20	5.70	3.00
3	5.00	9.70	8.20	4.40
4	7.50	12.20	10.70	4.80
5	10.00	14.70	13.20	4.80
6	12.50	17.20	15.70	4.80
7	15.00	19.70	18.20	4.80
8	17.50	22.20	20.70	4.80
9	20.00	24.70	23.20	4.80
10	22.50	27.20	25.70	4.80
11	25.00	29.70	28.20	4.80
12	27.50	32.20	30.70	4.80
13	30.00	34.70	33.20	4.80
14	32.50	37.20	35.70	4.80
15	35.00	39.70	38.20	4.80
16	37.50	42.20	40.70	4.80



SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Wafer PA66
PIN Brass Tin-plated

1	外壳	PA66	白色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	胶壳
料号 PART NO	HC-XA2. 54-5Y

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

X±0.25 X'±2'

单 位
UNIT

MM

X±0.25 X'±1'

张 数
PART NO

1 OF 1

.XX±0.15 .XX'±0.5'

版 本
REV

A

.XXX±0.10 .XXX'±0.5'

制 图
DRAW审 核
CHECKED

AhYe

夏操云

赵亮亮

