








Pin	DIM A	DIM B	DIM C
2	2.50	7.50	6.00
3	5.00	10.00	8.50
4	7.50	12.50	11.00
5	10.00	15.00	13.50
6	12.50	17.50	16.00
7	15.00	20.00	18.50
8	17.50	22.50	21.00
9	20.00	25.00	23.50
10	22.50	27.50	26.00
11	25.00	30.00	28.50
12	27.50	32.50	31.00
13	30.00	35.00	33.50
14	32.50	37.50	36.00
15	35.00	40.00	38.50
16	37.50	42.50	41.00



PCB LAYOUT

- 1.Current Rating:3A AC, DC
- 2.Voltage Rating:250V AC, DC
- 3.Temperatuer Range:−25°C~+85°C
- 4.Contact Resistance:20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material:Wafer PA66
PIN Brass Tin-plated

	深圳市虹成电子有限公司				品 名	针座	
					TITLE		
					料 号	HC-XA2. 54-6AW	
GENERAL TOLERANCES (UNLESS SPECIFIED)					比 例 SCALE	1 : 1	
X.±0.25	X.±2°	单 位 UNIT	MM	制 图 DRAW	AhYe		
.X±0.25	.X±1°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云		
.XX±0.15	.XX±0.5°	版 本 REV	A	批 准 APPROVED	赵亮亮		
.XXX±0.10	.XXX±0.5°						