






REV.	Q'TY	ECN. NO.	APR.	DATE




A-A

Technical requirements

Characteristic impedance	50Ω
Frequency range	0-3GHz
Contact resistance	
Inner conductor	≤3mΩ
Outer conductor	≤2mΩ
Insulated resistance	≥5000MΩ
Salt spray time	48H
Separation force	≥0.28N

Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc



PCB WELDING DRAWING (TOLERANCE: ±0.05)

1	铜座	1	黄铜	镀金
2	尖头焊针	1	黄铜	镀金
3	绝缘体	1	PTFE	
序号	名称	数量	材料	备注

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*±5°	APR.	Alex	TITLE: 1.5-半圆孔-H13.5	
.XX±0.25	.X.*±1	CHK.	Jack	DWG NO. XY-SMA-KE-P001	
.XXX±0.15	.XX.*±	DRA.	Can	PROJ.  CUSTOMER DRAWING	
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A