






|             |                                 |               |             |                |
|-------------|---------------------------------|---------------|-------------|----------------|
| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|             |                                 |               |             |                |
|             |                                 |               |             |                |




| PIN   | 尺寸 (mm) |       |       |
|-------|---------|-------|-------|
|       | A       | B     | C     |
| 02AWD | 2.50    | 7.50  | 6.20  |
| 03AWD | 5.00    | 10.00 | 8.70  |
| 04AWD | 7.50    | 12.50 | 11.20 |
| 05AWD | 10.00   | 15.00 | 13.70 |
| 06AWD | 12.50   | 17.50 | 16.20 |
| 07AWD | 15.00   | 20.00 | 18.70 |
| 08AWD | 17.50   | 22.50 | 21.20 |
| 09AWD | 20.00   | 25.00 | 23.70 |
| 10AWD | 22.50   | 27.50 | 26.20 |
| 11AWD | 25.00   | 30.00 | 28.70 |
| 12AWD | 27.50   | 32.50 | 31.20 |



SPECIFICATIONS  
1.Current Rating:3A AC, DC  
2.Voltage Rating:250V AC, DC  
3.Temperatuer Range: -25°C~+85°C  
4.Contact Resistance:20mΩ Max  
5.Insulation Resistance: 1000MΩ Min  
6.Withstanding Voltang: 1000V AC/minute  
7.Material:Wafer PA66  
PIN Brass Tin-plated



|     |     |      |       |     |
|-----|-----|------|-------|-----|
| 2   | 插针  | 铜    | 镀锡    |     |
| 1   | 基座  | PA66 | 白色    |     |
| 序 号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |

|                                                                                                   |            |                |              |                                                                                       |
|---------------------------------------------------------------------------------------------------|------------|----------------|--------------|---------------------------------------------------------------------------------------|
|  深圳市虹成电子有限公司 |            | 品 名<br>TITLE   | 针座           |                                                                                       |
|                                                                                                   |            | 料 号<br>PART NO | 5264-8AWD-TW |                                                                                       |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                                          |            | 比 列<br>SCALE   | 1:1          |  |
| X±0.25                                                                                            | X*±2°      | 单 位<br>UNIT    | MM           | 制 图<br>DRAW                                                                           |
| .X±0.25                                                                                           | .X*±1°     | 张 数<br>PART NO | 1 OF 1       | 审 核<br>CHECKED                                                                        |
| .XX±0.15                                                                                          | .XX*±0.5°  | 版 本<br>REV     | A            | 批 准<br>APPROVE                                                                        |
| .XXX±0.10                                                                                         | .XXX*±0.5° |                |              | 夏操云                                                                                   |
|                                                                                                   |            |                |              | 赵亮亮                                                                                   |

