

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN

尺寸 (mm)

A

B

C

02

2.50

7.40

6.50

03

5.00

9.90

9.00

04

7.50

12.40

11.50

05

10.00

14.90

14.00

06






12.50

17.40


16.50

SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Wafer PA66
PIN Brass Tin-plated



Circuit 1



1	基座	PA66	本色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	胶壳	
			料号 PART NO	HC-JK-5264-6Y	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X±0.25	X*±2°	单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.25	.X*±1°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15	.XX*±0.5°	版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10	.XXX*±0.5°				