

备注:

1. 材质:

1.1 胶芯: LCP+30%G.F

1.2 端子: C1814, T=0.12mm; 镀半金锡

1.3 外壳: 不锈钢, T=0.30mm; 表面镀镍

1.4 卡片: 不锈钢, T=0.15mm; 镀锡

1.5 接地片: 不锈钢, T=0.10mm;

2. 主要特性:

2.1 额定电流: 3A

2.2 接触阻抗: 40mΩ MAX

2.3 绝缘阻抗: 100MΩ MIN 250V DC

2.4 耐压测试: 100V AC

2.5 沾锡性: 温度 $245\pm 5^{\circ}\text{C}$, 时间 $5\pm 0.5\text{S}$

2.6 整体插入力: 2.0kgf MAX

耐久前整体拔出力: 0.8kgf MIN

耐久后整体拔出力: 0.6kgf MIN

2.7 使用寿命: 10000次

2.8 工作温度: $-25^{\circ}\text{C}\sim +80^{\circ}\text{C}$

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: USB TYPE-C/F 规格SMT 规格2.0		
.X ± 0.35	X.* $\pm 5^{\circ}$	Alex	DWG NO. XY-U262-4BV64-241N		
.XX ± 0.25	.X.* $\pm 3^{\circ}$	Jack	PROJ.  CUSTOMER DRAWING		
.XXX ± 0.15	.XX.* $\pm 1^{\circ}$	Can	SIZE A4	SCALE 1:1	SHEET 1/1
				REV. A	

