

备注:

1) 材质:








- 1-1 本体:LCP 94V-0 黑色
1-2 端子:C2680 T=0.15mm
1-3 钢壳:C2680 T=0.50mm

2) 镀层:


- 2-1 端子:所有面镀镍,接点镀金(参照料号编码),
焊脚镀锡 50u"MIN,盐雾测试48H无氧化生锈,锡区除外

3) 技术规格

- 3-1.额定电压:40V
3-2.额定电流:0.5A
3-3.绝缘电阻:100兆欧最小
3-4.接触电阻:30毫欧最大
3-5.操作温度:-20度到85度
3-6.插入力:44.1N Max
3-7.拔出力:9.8~39.2N;
3-8.耐久:10000次



COPLARNITY



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

3	CONTACT	19	C2680R-H	PLATED Au
2	SHELL	1	C2680R-H	PLATED NI
1	HOUSING	1	LCP	UL94V-0,Black
NO.	ITEM	Q'TY	DESCRIPTION	FINISH

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: HDMI 19P A/F 2.1VER		
.X±0.35	X.*± 5°	Alex	DWG NO. XY-HDMI-01-19PIN		
.XX±0.25	.X°± 3°	Jack	PROJ. CUSTOMER DRAWING		
.XXX±0.15	.XX°± 1°	Can	SIZE A4	SCALE 1:1	SHEET 1/1
			REV.	A	

装产品部分

20

备注 载带前空10格,中间装450PCS产品,后空10格

客户使用出料方向

四周角落填充三角垫

纸箱内上下各垫一层纸板

标签

防水袋

PCS/卷	卷/箱	PCS/箱
450	10	4500

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd			
.X±0.35	X:± 5°	APR. Alex	TITLE: HDMI 2.1 A/F 线材		
.XX±0.25	.X± 3°	CHK. Jack	DWG NO. XY-HDMI-01-19PIN		
.XXX±0.15	.XX*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1