








技术指标(Technical Index):


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
2. 工作温度(Temperature range): -25°C~+85°C.
3. 额定电压(Rated voltage): 250V, AC/DC.
4. 额定电流: 3.0A, AC/DC.
5. 接触电阻(Contact resistance): ≤20mΩ.
6. 绝缘电阻(Insulation resistance): ≥1000MΩ.
7. 耐电压(Withstanding Voltage): 800V AC/minute.



Part No	CKT	A	B	C	D
ZX-PA2.0-2PLT-BD	2	2.00	4.55	7.95	6.10
ZX-PA2.0-3PLT-BD	3	4.00	6.55	9.95	8.10
ZX-PA2.0-4PLT-BD	4	6.00	8.55	11.95	10.10
ZX-PA2.0-5PLT-BD	5	8.00	10.55	13.95	12.10
ZX-PA2.0-6PLT-BD	6	10.00	12.55	15.95	14.10
ZX-PA2.0-7PLT-BD	7	12.00	14.55	17.95	16.10
ZX-PA2.0-8PLT-BD	8	14.00	16.55	19.95	18.10
ZX-PA2.0-9PLT-BD	9	16.00	18.55	21.95	20.10
ZX-PA2.0-10PLT-BD	10	18.00	20.55	23.95	22.10
ZX-PA2.0-11PLT-BD	11	20.00	22.55	25.95	24.10
ZX-PA2.0-12PLT-BD	12	22.00	24.55	27.95	26.10
ZX-PA2.0-13PLT-BD	13	24.00	26.55	29.95	28.10
ZX-PA2.0-14PLT-BD	14	26.00	28.55	31.95	30.10
ZX-PA2.0-15PLT-BD	15	28.00	30.55	33.95	32.10
ZX-PA2.0-16PLT-BD	16	30.00	32.55	35.95	34.10

序号	品名	材质
①	2.0 R型立式WTB胶芯 2.0 Pitch R/A Wire To Board Housing(H=5.7)	PA6T UL94V-0 米黄色 LCP UL94V-0 本色
②	2.0 R型立式WTB端子 2.0 Pitch S/T Wire To Board Terminal(H=8.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	2.0 R型立式WTB焊片 2.0 Pitch R/A Wire To Board Fitting Nail(H=5.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
④	2.0 R型立式WTB吸盖 2.0 Pitch S/T Wire To Board Cover(H=8.7)	LCP UL94V-0 黑色/本色

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			X.:±0.50	±1°	审核 CHECK
			X.X:±0.20		批准 APPROVAL
			X.XX:±0.10		单位 UNITS

ROSE			料号 PART NO.	ZX-PA2.0-NPLT-BD	版本 REV.	A
LEO			品名 TITLE	2.00 Pitch R型立式WTB	页次 SHEET	1/1
JOHN			客户料号 CUTM.NO.			
MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			