

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A

B

C

D

E

F

G

A

B



C

D

E




F

G



SPECIFICATIONS

- 1.Current Rating:3A AC, DC
- 2.Voltage Rating:250V AC, DC
- 3.Temperatuer Range:−25℃~+85℃
- 4.Contact Resistance:30mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material:Phosphoric bronze Tin-plated
- 8.Applicable Wire Sizes:AWG#22~30#



1	端子	铜	镀锡	
序号	品名	材质	电镀/颜色	备注
品名 TITLE		端子		
料号 PART NO		HC-DZ-XHD2.54-S		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1	
X.X±0.25	X.*±2°	单位 UNIT	MM	制图 DRAW
X.XX±0.20		张数 PART NO	1 OF 1	审核 CHECKED
X.XXX±0.10		版本 REV	A	批准 APPROVE

深圳市虹成电子有限公司