









LOCK CONFIGURATION(锁扣位置)



With Cap



技术指标(Technical Index):



- 1.塑件表面应光洁,无毛边,无明显收缩、缺陷、裂纹等现象.(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 2.锁扣窗口:2~3PIN为1个,≥4PIN为2个.
(Lock Configuration:2 to 3Pin is 1,≥4Pin is 2)
- 3.温度范围(Temperature range):-25°C~+85°C.
- 4.额定电流 Rated Current:1A AC/DC
- 5.额定电压(Rated voltage):125V,AC/DC(=等效).
- 6.接触电阻(Contact resistance):≤0.02Ω.
- 7.绝缘电阻(Insulation resistance):≥100MΩ

Part No	CKT	A	B	C
BX-MX1.25-2PZZ-BD	2	1.25	3.20	4.30
BX-MX1.25-3PZZ-BD	3	2.50	4.45	5.55
BX-MX1.25-4PZZ-BD	4	3.75	5.70	6.80
BX-MX1.25-5PZZ-BD	5	5.00	6.95	8.05
BX-MX1.25-6PZZ-BD	6	6.25	8.20	9.30
BX-MX1.25-7PZZ-BD	7	7.50	9.45	10.55
BX-MX1.25-8PZZ-BD	8	8.75	10.70	11.80
BX-MX1.25-9PZZ-BD	9	10.00	11.95	13.05
BX-MX1.25-10PZZ-BD	10	11.25	13.20	14.30
BX-MX1.25-11PZZ-BD	11	12.50	14.45	15.55
BX-MX1.25-12PZZ-BD	12	13.75	15.70	16.80
BX-MX1.25-13PZZ-BD	13	15.00	16.95	18.05
BX-MX1.25-14PZZ-BD	14	16.25	18.20	19.30
BX-MX1.25-15PZZ-BD	15	17.50	19.45	20.55
BX-MX1.25-16PZZ-BD	16	18.75	20.70	21.80
BX-MX1.25-17PZZ-BD	17	20.00	21.95	23.05
BX-MX1.25-18PZZ-BD	18	21.25	23.20	24.30
BX-MX1.25-19PZZ-BD	19	22.50	24.45	25.55
BX-MX1.25-20PZZ-BD	20	23.75	25.70	26.80

序号	品名	材质
①	A型立式DIP型WTB胶芯 1.25 Pitch S/T Wire To Board Housing DIP(H=4.7)	LCP UL94V-0 本色 Natural
②	A型立式DIP型WTB端子 1.25 Pitch S/T Wire To Board Terminal DIP(H=4.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	A型立式DIP型WTB吸盖 1.25 Pitch S/T Wire To Board Cap	LCP UL94V-0 本色




制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		
			X.±0.50	±1°	审核 CHECK	EVA		
			.X±0.20		核准 APPROVAL	JADE		
			.XX±0.10					
					单位 UNITS	MM	比例 SCALE	1:1






制图 DRAWN	変更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	
			.X±0.50	±1°
			.X±0.25	
			.XX±0.15	

9. 纸箱分小、中、标准型3种规格型号:装箱为整箱(左下包装量)采用标准型纸箱包装,未达整箱数量以产品量适当采用小型或中型纸箱包装。



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Hight (CM)	7.5	15	32

CKT (1.25mm pitch)	B0	W	F	S
2	4.60	16	7.50	
3	5.85	24	11.50	
4	7.10			
5	8.35			
6	9.60			
7	10.85			
8	12.10			
9	13.35			
10	14.60	32	14.2±0.10	28.45
11	15.85			
12	17.10			
13	18.35			
14	19.60	44	20.2±0.15	40.45
15	20.85			
16	22.10			
17	23.35			
18	25.85			
19	28.35			
20	30.85			

料号 PART NO.	BX-MX1.25-NPZZ-BD	版本 REV.	A
品名 TITLE	1.25-A型直针WTB载带包装	页次 SHEET	1/1
客户料号 CUTM.NO.			
 Bossie (博锡)			



Bossie (博锡)